



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## F72T12CWH0 85W T12 72" Cool White High Output 62 Cri R17D

*Sylvania-Ledvance*

Catalog Number	F72T12CWH0
Manufacturer	Sylvania-Ledvance
Description	85W, 72" Mol, T12 Ho (800 Ma) Rapid Start Fluorescent Lamp, Cool Whitephosphor, 4200K Color Temperature, 60 Cri
Weight per unit	1.1 (lbs/each)
Product Category	Linear Fluorescent Straight La

### Features

amperage rating	Ballast Dependent
Base	Recessed Double Contact
Lamp Type	RAPID START
lumens	6250 Initial Lumens at 25 Degrees C
Shape	T12
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	85

### Material, Color, and Finish

color rendering index (cri)	60
color temperature	4200

### Descriptions

Description	85W T12 72" COOL WHITE HIGH OUTPUT 62 CRI R17D
extra long description	SYL F72T12/CW/HO/25176 F72T12CWH0 1
Long Description	85W, 72"MOL, T12 HO (800 mA) rapid start fluorescent lamp, Cool Whitephosphor, 4200K color temperature, 60 CRI
Special Features	COOL WHITE

### Manufacturer Information

Brand	SYLVANIA
GTIN	00046135251764
Manufacturers Part Number	F72T12/CW/HO/25176
UPC	046135251764

### Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

### Packaging

Carton	1
Package	15
Weight Per each	1.08

### Uses, Certifications, and Standards

Application	Commercial/Residential
-------------	------------------------