ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

F84T12DH0 100W T12 84" Daylight High Output 76 Cri R17D

Sylvania-Ledvance

Catalog Number	F84T12DH0
Manufacturer	Sylvania-Ledvance
Description	100W, 84" Mol, T12 Ho (800 Ma) Rapid Start Fluorescent Lamp, Daylightphosphor, 6500K Color Temperature, 72 Cri
Weight per unit	1.3 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

amperage rating	Ballast Dependent
average life	12000
Base	Recessed Double Contact
bulb type	T12
lumens	6700 Initial Lumens at 25 Degrees C
Shape	T12
start type	Rapid Start
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	100

Material, Color, and Finish

color rendering index (cri)	76
color temperature	6500
Finish	Phosphor Coated

Dimensions and Weight

Diameter	1.5 in

Descriptions

Description	100W T12 84" DAYLIGHT HIGH OUTPUT 76 CRI R17D
extra long description	LDV F84T12DHO/25385 F84T12DHO 15/CS
Long Description	100W, 84" MOL, T12 HO (800 mA) rapid start fluorescent lamp, Daylightphosphor, 6500K color temperature, 72 CRI
Product Type	F84T12DHO 15/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135253850
Manufacturers Part Number	F84T12/D/HO/25385
UPC	046135253850

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	15
Weight Per each	1.26

Uses, Certifications, and Standards

Application	Commercial/Residential