



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F96T12CWSSUPC Lamp F96T12/CWX/SS/Upc *Sylvania-Ledvance*

Catalog Number	F96T12CWSSUPC
Manufacturer	Sylvania-Ledvance
Description	60W, 96 Inch Mol, T12 Instant Start Slimline Super Saver Fluorescent Lamp, Cool White Deluxe Phosphor, 4100K Color Temperature, 87 Cri, Upc Code. Vivid Color: High Cri Lamps For Color Critical Applications
Weight per unit	1.4 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

amperage rating	Ballast Dependent
Base	Single Pin
bulb type	T12
Lamp Type	INSTANT START
lumens	3850
Shape	T12
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	60

Material, Color, and Finish

color rendering index (cri)	87
color temperature	4100

Descriptions

Description	LAMP F96T12/CWX/SS/UPC
extra long description	SYL F96T12CWSSUPC/23503 F96T12CWXS
Long Description	60W, 96 inch MOL, T12 instant start Slimline SUPER SAVER fluorescent lamp, Cool White Deluxe phosphor, 4100K color temperature, 87 CRI, UPC code. VIVID Color: High CRI lamps for color critical applications

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135235030
Manufacturers Part Number	23503
UPC	046135235030



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

Packaging

Carton	1
Package	15
Weight Per each	1.43