

Bulb Shape	Base	Watts	Nominal Length (in)	Order Code	Description	Case Qty	Rated Life (hrs)	Initial Lumens	Mean Lumens	Color Temp K	CRI	High Color Rendering	Energy Savings	Reduced Wattage	Meets Federal Minimum Efficiency Standards	Footnotes	Warning and Caution Notices	Additional Information
T12 Lamps (continued)																		
T12 High Output (800mA) Rapid Start Recessed Double Contact (continued)																		
30" High Output																		
T12	Recessed Double Contact (R17d)	40	30.0	33707	F30T12/CW/HO	24	9000	2250	1950	4100	60						101	
3' High Output																		
T12	Recessed Double Contact (R17d)	45	36.0	10374	F36T12/CW/HO	24	9000	2800	2440	4100	60						101	
		45	36.0	10380	F36T12/D/HO	24	9000	2350	2040	6500	75	☺					101	
		45	36.0	10388	F36T12/SGN/HO	24	9000	2150	1830	5400	82	☺					101	
42" High Output																		
T12	Recessed Double Contact (R17d)	55	42.0	10559	F42T12/CW/HO	24	9000	3200	2790	4100	60						101	
		55	42.0	10560	F42T12/D/HO	24	9000	2900	2520	6500	74	☺					101	Daylight
		55	42.0	10562	F42T12/SGN/HO	24	9000	2600	2215	5400	82	☺					101	Sign White
4' High Output																		
T12	Recessed Double Contact (R17d)	60	48.0	15359	F48T12/SP30/HO	24	12000	4250	3830	3000	70	☺					101	
		60	48.0	15360	F48T12/SP35/HO	24	12000	4250	3830	3500	73	☺					101	
		60	48.0	15361	F48T12/SP41/HO	24	12000	4250	3830	4100	72	☺					101	
		60	48.0	15115	F48T12/SPX35/HO	24	12000	4350	3920	3500	82	☺					101	
		60	48.0	10773	F48T12/CW/HO	24	12000	3825	3320	4100	60						101	
		60	48.0	27313	F48T12/CW/HO/UPC	24	12000	4050	3520	4100	60						101	
		60	48.0	10778	F48T12/D/HO	24	12000	3400	2960	6500	75	☺					101	Daylight
		60	48.0	10573	F48T12/SGN/HO	24	12000	3100	2640	5400	80	☺					101	Sign White
4' High Output Watt-Miser® Energy Saving Lamps																		
T12	Recessed Double Contact (R17d)	55	48.0	15342	F48T12/SP35/HO/WM	24	12000	3850	3465	3500	73	☺	\$	↗		1	101	
		55	48.0	11179	F48T12/LW/HO/WM	24	12000	3900	3390	4200	49		\$	↗		1	101	Lite White
5' High Output																		
T12	Recessed Double Contact (R17d)	75	60.0	23075	F60T12/CW/HO 15PK	15	12000	5150	4480	4100	60						101	
		75	60.0	23077	F60T12/D/HO 15PK	15	12000	4400	3830	6500	75	☺					101	Daylight
		75	60.0	23081	F60T12/SGN/HO 15PK	15	12000	4000	3400	5400	82	☺					101	Sign White
64" High Output																		
T12	Recessed Double Contact (R17d)	80	64.0	23083	F64T12/CW/HO/15PK	15	12000	5600	4870	4100	60						101	
		80	64.0	23087	F64T12/D/HO/15PK	15	12000	4750	4130	6500	75	☺					101	Daylight
		80	64.0	23089	F64T12/SGN/HO/15PK	15	12000	4300	3660	5400	82	☺					101	Sign White
6' High Output																		
T12	Recessed Double Contact (R17d)	85	72.0	15343	F72T12/SP30/HO/15PK	15	12000	6650	5990	3000	70	☺					101	
		85	72.0	15347	F72T12/SP35/HO/15PK	15	12000	6650	5990	3500	73	☺					101	
		85	72.0	15348	F72T12/SP41/HO/15PK	15	12000	6650	5990	4100	72	☺					101	
		85	72.0	15137	F72T12/SPX30/HO/15P	15	12000	6800	6120	3000	82	☺					101	
		85	72.0	15351	F72T12/SPX35/HO/15P	15	12000	6800	6120	3500	82	☺					101	
		85	72.0	13697	F72T12/CW/HO/15PK	15	12000	6350	5520	4100	60						101	
		85	72.0	13699	F72T12/D/HO/15PK	15	12000	5350	4650	6500	75	☺					101	Daylight
		85	72.0	12527	F72T12/N/HO	10	12000	4300	3610	3700	90	☺					101	Natural
		85	72.0	13701	F72T12/SGN/HO/15PK	15	12000	4900	4170	5400	82	☺					101	Sign White
		85	72.0	13702	F72T12/WW/HO/15PK	15	12000	6550	5700	3000	52						101	Warm White
		7' High Output																
T12	Recessed Double Contact (R17d)	100	84.0	13766	F84T12/CW/HO/15PK	15	12000	7700	6700	4100	60						101	
		100	84.0	13767	F84T12/D/HO/15PK	15	12000	6500	5660	6500	75	☺					101	Daylight
		100	84.0	13768	F84T12/SGN/HO/15PK	15	12000	6000	5100	5400	82	☺					101	Sign White
8' High Output																		
T12	Recessed Double Contact (R17d)	110	96.0	15362	F96T12/SP30/HO/15PK	15	12000	9200	8280	3000	70	☺			Ⓢ		101	
		110	96.0	15363	F96T12/SP35/HO/15PK	15	12000	9200	8280	3500	73	☺			Ⓢ		101	
		110	96.0	15364	F96T12/SP41/HO/15PK	15	12000	9200	8280	4100	72	☺			Ⓢ		101	
		110	96.0	12130	F96T12/SP65/HO	15	12000	8900	8010	6500	75	☺			Ⓢ		101	
		110	96.0	15119	F96T12/SPX30/HO/15PK	15	12000	9350	8420	3000	82	☺			Ⓢ		101	
		110	96.0	15352	F96T12/SPX35HO15PK	15	12000	9350	8420	3500	82	☺			Ⓢ		101	
		110	96.0	23070	F96T12/SPX41/HO/15PK	15	12000	9350	8420	4100	80	☺			Ⓢ		101	
		110	96.0	13707	F96T12/C50/HO/15PK	15	12000	6750	5670	5000	90	☺					101	Chroma 50
		110	96.0	14653	F96T12/DX/HO	15	12000	6600	5610	6500	84	☺				Ⓢ	101	Daylight Deluxe

For the most up-to-date product information, see www.gelighting.com. To convert inches to millimeters, multiply by 25.4. All footnotes, warning and caution notices found at the end of this section (page 4-32).