



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FB032735ECO 32W T8 22.5" 6" Leg Spacing 3500K 75 Cri Bi-Pin

Sylvania-Ledvance

Catalog Number	FB032735ECO
Manufacturer	Sylvania-Ledvance
Description	32W, 22.5" Mol, T8 Octron Curvalume Fluorescent Lamp, 6" Leg Spacing, 3500K Color Temperature, Rare Earth Phosphor, 75 Cri, Suitable For Is or RS Operation, Ecologic
Weight per unit	0.5600 (lbs/each)
Product Category	Shape Lamps

Features

amperage rating	Ballast Dependent
average life	20000
Base	Medium Bipin
bulb type	T8
Lamp Type	CURVALUME
lumens	2750 Initial Lumens at 25 Degrees C
Shape	T8
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	32

Material, Color, and Finish

color rendering index (cri)	75
color temperature	3500
Finish	Phosphor Coated

Dimensions and Weight

Diameter	1
----------	---

Descriptions

Description	32W T8 22.5" 6" LEG SPACING 3500K 75 CRI BI-PIN
extra long description	SYL FBO32/735/6/ECO/22051 FBO327356
Long Description	32W, 22.5" MOL, T8 OCTRON Curvalume fluorescent lamp, 6" leg spacing, 3500K color temperature, rare earth phosphor, 75 CRI, suitable for IS or RS operation, ECOLOGIC
Product Type	FBO327356ECO 16/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135220517
Manufacturers Part Number	FBO32/735/6/ECO/22051
UPC	046135220517



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
Type	FLUORESCENT

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
Package	16
Weight Per each	0.56

Uses, Certifications, and Standards

Application	Commercial/Residential
standard	C78.1-1991