

More on reverse!

Plated Steel Fan/Fixture Box

with Fully Adjustable Mounting Brackets

FBR415
Steel
Fan/Fixture Box

New!

Arlington's new super heavy-duty, plated steel fan/fixture box is the innovative alternative to existing bar hanger brackets. Its heavy-duty construction eliminates the fan wobble you get with lighter weight products. Plus, FBR415 ships ready to use, with all mounting hardware secured in the assembly. There are no bagged parts or pieces to lose!

The **FBR415** Fan/Fixture Box...

- Works on ceilings up to 1-1/4" thick

Mounts easily and securely between joists

- Adjusts from 16" to 24" o.c.

Self-contained.
No pieces to lose!

This 15.6 cubic inch volume box is UL Listed for fans and fixtures up to 70 lbs.

For added convenience and ease of use, it ships with mud cover in place and installed NM cable connector. It's completely self-contained, with no pieces to lose. Competitively priced too!



Arlington

1 Stauffer Industrial Park, Scranton, PA 18517

800/233-4717 • FAX 570/562-0646

www.aifittings.com







Patent pending

FBR415 0404/50M


©2004 Arlington Industries, Inc.

Heavy-Duty Fan/Fixture Box

Versatile 16" to 24" On-Center Positioning




FULLY ADJUSTABLE!



Install fan/fixture flush with ceilings up to 1-1/4" thick, by bending the bracket along the scoreline that

matches your ceiling depth.

FBR415 Adjustable Heavy-Duty Plated Steel Fan/Fixture Box



Arlington

1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.aifittings.com

Distributed by

Catalog Number	UPC/DCI/NAED MFG #01 8997	For Ceiling Thickness	Std Pkg
FBR415	72250	up to 1-1/4"	10

More on reverse!

Plated Steel Fan/Fixture Box

with Fully Adjustable Mounting Brackets

FBR415
Steel
Fan/Fixture Box

New!

Arlington's new super heavy-duty, plated steel fan/fixture box is the innovative alternative to existing bar hanger brackets. Its heavy-duty construction eliminates the fan wobble you get with lighter weight products. Plus, FBR415 ships ready to use, with all mounting hardware secured in the assembly. There are no bagged parts or pieces to lose!

The **FBR415** Fan/Fixture Box...

- Works on ceilings up to 1-1/4" thick

Mounts easily and securely between joists

- Adjusts from 16" to 24" o.c.

Self-contained.
No pieces to lose!

This 15.6 cubic inch volume box is UL Listed for fans and fixtures up to 70 lbs.

For added convenience and ease of use, it ships with mud cover in place and installed NM cable connector. It's completely self-contained, with no pieces to lose. Competitively priced too!



Arlington

1 Stauffer Industrial Park, Scranton, PA 18517

800/233-4717 • FAX 570/562-0646

www.aifittings.com







Patent pending

FBR415 0404/50M


©2004 Arlington Industries, Inc.

Heavy-Duty Fan/Fixture Box

Versatile 16" to 24" On-Center Positioning




FULLY ADJUSTABLE!



Install fan/fixture flush with ceilings up to 1-1/4" thick, by bending the bracket along the scoreline that

matches your ceiling depth.

FBR415
Adjustable
Heavy-Duty
Plated Steel
Fan/Fixture Box



Arlington

1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.aifittings.com

©2004 Arlington Industries, Inc.

Distributed by

Catalog Number	UPC/DCI/NAED MFG #01 8997	For Ceiling Thickness	Std Pkg
FBR415	72250	up to 1-1/4"	10