More on

Plated Steel Fan/Fixture Box

with Fully Adjustable Mounting Brackets



Self-contained.

No pieces to lose!

Arlington's new super heavy-duty, plated steel fan/fixture box is the innovative alternative to existing bar hanger brackets. Its heavy-duty construction eliminates the fan wobble you get with lighter weight products. Plus, FBRS415 ships ready to use, with all mounting hardware secured in the assembly. There are no bagged parts or pieces to lose!

The FBRS415 Fan/Fixture Box...

 Works on ceilings up to 1-1/4" thick

Mounts easily and securely between joists

• Adjusts from 16" to 24" o.c.



This 15.6 cubic inch volume box is UL Listed for fans and fixtures up to 70 lbs.

For added convenience and ease of use, it ships with mud cover in place and installed NM cable connector. It's completely self-contained, with no pieces to lose. Competitively priced too!





Arlington

1 Stauffer Industrial Park. Scranton, PA 18517 800/233-4717 • FAX 570/562-0646 www.aifittings.com

FBRS415 0404/50M

Patent pending

©2004 Arlington Industries, Inc.

Heavy-Duty Fan/Fixture Box

Versatile 16" to 24" On-Center Positioning









Use these screws to install fan mounting bracket.



Adjust box position from 16" to 24" on-center between joists with this screw

"Tooth" holds bracket temporarily in place

FULLY ADJUSTABLE!




Install fan/fixture flush with ceilings up to 1-1/4" thick, by bending the bracket along the scoreline that

matches your ceiling depth.

Arlington

1 Stauffer Industrial Park Scranton, PA 18517 800/233.4717 Fax 570/562.0646 www.aifittings.com FBRS415 Adjustable Heavy-Duty Plated Steel Fan/Fixture Box

Distributed by



Catalog Number	UPC/DCI/NAED MFG #01 8997		
FBRS415	72250	up to 1-1/4"	10

©2004 Arlington Industries, Inc.