

---

## SUPPORT GRIPS STANDARD DUTY, CLOSED MESH

FC075U | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

Standard-duty, Closed mesh, Single eye grips. Cable diameter - 0.750-0.990", Bale length - 8", Mesh length - 14", Break Strength - 1,300 lbs.

- Standard closed mesh support grips are designed for loads up to 600 lbs.
- Vertical runs of no more than 100 ft.
- They are available in a variety of eye styles and cable ranges for supporting electrical and fiber optic cable, metal rods, and tubing.
- Closed mesh support grips are used when the end of the cable is accessible.
- Support grips are woven of corrosion-resistant tinned-bronze wire.
- Most Flexcor products have UL and/or CSA approvals. Please contact factory for approval information.

---

### SPECIFICATIONS

#### GENERAL INFO

Typical Applications: Service Drop  
Product Series: Flexcor  
Type: Closed Mesh  
Duty: Standard Duty  
Special Features: Single Eye

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: Yes  
CUL Listing No: No  
cULus: No  
cURus: No  
Federal Spec: No  
UL Listing No: No  
UN SPSC: 39121722  
UR: No

#### DIMENSIONS

Weight: 0.15759

**BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

