Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FNCFBHB 4" RND Draft Tight Ceilimng BX/Bar HNGR

Abb Installation Products, Inc

Catalog Number	FNCFBHB
Manufacturer	Abb Installation Products, Inc
Description	Round Fan/Fixture Vaportight Box, Volume 26 Cubic Inches, Diameter 4 Inches, Depth 2-3/4 Inches, Color Black, Polycarbonate, Mounting Means #3 Bracket, Mounting Means 16 Inch to 24 Inch Adjustable Hanger Bar
Weight per unit	2.1 (lbs/each)
Product Category	Ceiling Fan Parts & Accy.

Features

Knockouts	Yes
Material	Polycarbonate

Material, Color, and Finish

Color	Black

Descriptions

Description	4" RND DRAFT TIGHT CEILIMNG BX/BAR HNGR
extra long description	TB FN-CFB-HB DRAFT TIGHT CEILING FA
Long Description	Round Fan/Fixture Vaportight Box, Volume 26 Cubic Inches, Diameter 4 Inches, Depth 2-3/4 Inches, Color Black, Polycarbonate, Mounting Means #3 Bracket, Mounting Means 16 Inch to 24 Inch Adjustable Hanger Bar
Product Type	Draft Tight Ceiling Fan Box W/Bar
Special Features	High-strength polycarbonate construction will not shatter when cold

Manufacturer Information

Brand	Carlon
GTIN	00034481013327
Manufacturers Part Number	FN-CFB-HB
UPC	034481013327

Taxonomies, Classifications, and Categories

Category Description	PLASTIC BOXES

Packaging

Carton	6
Weight Per each	2.14

Uses, Certifications, and Standards

standard	UL E11461