

## ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2 Solar Circle 30265-0000, GA Newnan Phone: 678-621-2507 Fax: 678-621-2508



## FNM1610 1-6/10A 250V TD Midget Fuse Bussmann Fuses

bussinaiii i uses	
Catalog Number	FNM1610
Manufacturer	Bussmann Fuses
Description	Eaton Bussmann Series FNM Fuse, Time-Delay, 1.6 A, Dual, Non-Indicating, Ferrule End X Ferrule End, 10 Kaic At 125 Vac, 100 Aic At 250 Vac, Nickel-Plated Bronze Endcap, Standard, 250 V
Weight per unit	0.0200 (lbs/each)
Product Category	Small Dimension Fuses
Features	
amperage rating	1-6/10 Amp
class	Supplemental
connection	
dimensions	0.3900 IN X 0.3900 IN X 1.4400 IN
element	Decel
interrupt rating	100 Amp at 250 Vac, 10000 Amp at 125 Vac
Material	Nickel-plated bronze endcap
media	Yes
Voltage Rating	250 VAC
<b>Dimensions and Weight</b>	
Size	13/32 In Diameter X 1-1/2 In Length
Descriptions	
Description	1-6/10A 250V TD MIDGET FUSE
extra long description	BUSS FNM-1-6/10 BUSS MIDGET FUSE
Features	Bussmann offers the broadest selection of Supplemental and Midget fuses in both time-delay and fast-acting designs with voltages as high as 600Vac and 600Vdc.
Long Description	Eaton Bussmann series FNM fuse, Time-delay, 1.6 A, Dual, Non-indicating, Ferrule end x ferrule end, 10 kAIC at 125 Vac, 100 AIC at 250 Vac, Nickel-plated bronze endcap, Standard, 250 V
Product Type	Buss Midget Fuse
Special Features	Nickle Plated Brass Endcap
Manufacturer Information	
Brand	Eaton Bussmann series
GTIN	00051712520164

## Ma

Brand	Eaton Bussmann series
GTIN	00051712520164
Manufacturers Part Number	FNM-1-6/10
UPC	051712520164



standard

## ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2 Solar Circle 30265-0000, GA Newnan Phone: 678-621-2507 Fax: 678-621-2508

Taxonomies, Classifications, and Categories		
Category Description	MIDGET FUSES	
Туре	FUSE	
Packaging		
Carton	10	
Weight Per each	0.02	
Uses, Certifications, and Standards		
Application	Ind Facilities & Factories - Facility: Safety and Security Systems	

RoHS Compliant, CE Marked