ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
1821 North Topping Avenue
64120-0000, MO Kansas City
Phone: 913-227-4257
Fax: 816-656-2196



FNM20 250V Ac TD Midget Fuse

Bussmann Fuses

Catalog Number	FNM20
Manufacturer	Bussmann Fuses
Description	Eaton Bussmann Series FNM Fuse, Time-Delay, 20 A, Dual, Non-Indicating, Ferrule End X Ferrule End, 10 Kaic At 250 Vac, Nickel-Plated Bronze Endcap, Standard, 250 V
Weight per unit	0.0200 (lbs/each)
Product Category	Small Dimension Fuses

Features

amperage rating	20 Amp
class	Supplemental
connection	Ferrule End X Ferrule End
dimensions	0.3900 IN X 0.3900 IN X 1.4400 IN
element	Dual
interrupt rating	10000 Amp
Material	Nickel-plated bronze endcap
Voltage Rating	250 VAC

Dimensions and Weight

Size	13/32 In Diameter X 1-1/2 In Length

Descriptions

Description	250V AC TD MIDGET FUSE
extra long description	BUS FNM-20 BUSS MIDGET FUSE
Features	Bussmann offers the broadest selection of Supplemental and Midget fuses in both time-delay and fast-acting designs with voltages as high as 600Vac and 600Vdc.
Long Description	Eaton Bussmann series FNM fuse, Time-delay, 20 A, Dual, Non-indicating, Ferrule end x ferrule end, 10 kAIC at 250 Vac, Nickel-plated bronze endcap, Standard, 250 V
Product Type	Buss Midget Fuse
Special Features	Nickle Plated Brass Endcap

Manufacturer Information

Brand	Eaton
GTIN	00051712522007
Manufacturers Part Number	FNM-20
UPC	051712522007

Taxonomies, Classifications, and Categories

Category Description	MIDGET FUSES
Type	FUSE

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
1821 North Topping Avenue
64120-0000, MO Kansas City
Phone: 913-227-4257
Fax: 816-656-2196

Packaging

Carton	10
Weight Per each	0.02

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Safety and Security Systems
standard	Contact factory,CE Marked,RoHS Compliant