

# ELLIOTT ELECTRIC SUPPLY 3942 Automation Way 80525-0000, CO Fort Collins Phone: 970-305-3593 Fax: 970-372-1731



# FNQ110 1/10A 500V TD CT Midget Fuse Bussmann Fuses

Catalog Number	FNQ110
Manufacturer	Bussmann Fuses
Description	Eaton Bussmann Series FNQ Fuse, Time-Delay, Motor Control Transformers, Circuits With In-Rush Currents, 0.1 A,
	Non-Indicating, Ferrule End X Ferrule End, 10 Kaic At 500 Vac,
	Nickel-Plated Bronze Endcap, Standard, 500 V
Weight per unit	0.0200 (lbs/each)
Product Category	Small Dimension Fuses

#### **Features**

amperage rating	1/10 Amp
class	Supplemental
connection	Ferrule End X Ferrule End
dimensions	0.4100 IN X 0.4100 IN X 1.5000 IN
interrupt rating	10000 Amp (RMS Symmetrical)
Material	Nickel-plated bronze endcap
media	Yes
Voltage Rating	500 VAC

## **Dimensions and Weight**

Size 13/32 In D	Diameter X 1-1/2 In Length
-----------------	----------------------------

### **Descriptions** Description

Description	1/10A 500V TD CT MIDGET FUSE
extra long description	BUSS FNQ-1/10 BUSS MIDGET FUSE
Features	Bussmann offers the broadest selection of Supplemental and Midget fuses in both time-delay and fast-acting designs with voltages as high as 600Vac and 600Vdc.
Long Description	Eaton Bussmann series FNQ fuse, Time-delay, Motor control transformers, Circuits with in-rush currents, 0.1 A, Non-indicating, Ferrule end x ferrule end, 10 kAIC at 500 Vac, Nickel-plated bronze endcap, Standard, 500 V
Product Type	Buss Midget Fuse
Special Features	Nickel Plated Brass Endcap

## **Manufacturer Information**

Brand	Eaton
GTIN	00051712786164
Manufacturers Part Number	FNQ-1/10
UPC	051712786164



Application

standard

# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3942 Automation Way 80525-0000, CO Fort Collins Phone: 970-305-3593 Fax: 970-372-1731

Ind Facilities & Factories - Facility: Safety and Security Systems

Taxonomies, Classifications, and C	ategories	
Category Description	MIDGET FUSES	
Tyne	FLISE	
Packaging		
Carton	10	
Weight Per each	0.02	
Uses, Certifications, and Standards	3	

CE Marked, RoHS Compliant