

# Eaton FNQ-5

Catalog Number: FNQ-5

Eaton Bussmann series FNQ fuse, Time-delay, Motor control transformers, Circuits with in-rush currents, 5 A, Non-indicating, Ferrule end x ferrule end, 10 kAIC at 500 Vac, Nickel-plated bronze endcap, Standard, 500 V



## General specifications

Product Name	Catalog Number
Eaton Bussmann series FNQ fuse	FNQ-5
UPC	EAN
051712786294	5027590060554
Product Length/Depth	Product Height
0.41 in	1.5 in
Product Width	Product Weight
0.41 in	0.175 lb
Warranty	Compliances
Not Applicable	CE Marked
	RoHS Compliant

## Electrical rating

### Amperage Rating

5 A

### Interrupt rating

10 kAIC at 500 Vac

### Voltage rating

500 V

## Physical details

### Material

Nickel-plated bronze endcap

### Packaging type

Standard

## General information

### Connection

Ferrule end x ferrule end

### Fuse indicator

Non-indicating

## Resources

### Catalogs

[FNQ-5-BUSS MIDGET FUSE](#)

[Bussmann series complete full line catalog no. 1007](#)

### Multimedia

[Bussmann series Fuseology](#)

### Specifications and datasheets

[Eaton Specification Sheet - FNQ-5](#)

### Technical service bulletins

[Datasheet - FNQ-30](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)