



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

204 Lake Road  
76426-0000, TX Bridgeport  
Phone: 940-683-5740  
Fax: 940-683-5299



## FNQR15 15A 600V TD Class CC Fuse

*Bussmann Fuses*

Catalog Number	FNQR15
Manufacturer	Bussmann Fuses
Description	Fuse, Time Delay Fuse Speed, Class CC Fuse, 12 S @ 200% Response Time, Ferrule End X Ferrule End Connection, 15 A, 600 V Ac;300 V DC, Melamine Material, 0.41 In Diameter, 1.5 In Overall Length, 0.02 LB
Weight per unit	0.0200 (lbs/each)
Product Category	Small Dimension Fuses

### Features

amperage rating	15
connection	Ferrule End X Ferrule End
dimensions	1.5000 IN X 0.4100 IN X 0.4100 IN

### Dimensions and Weight

Size	13/32 In Diameter X 1-1/2 In Length
------	-------------------------------------

### Descriptions

Description	15A 600V TD CLASS CC FUSE
extra long description	BUSS FNQ-R-15 CLASS CC TIME DELAY
Features	Bussmann's Class CC fuses set the standard in Class CC fuse performance in the industry. Recognized for their superior performance, Bussmann has the right product for your circuit and equipment protection needs. These branch circuit rated, 600v, 200,000a IR fuses offer exceptional protection in the smallest package of any UL class of fuses. Choose from the ultimate protection provided by our Low Peak LP-CC fuses, the time delay of our FNQ-R's for your control transformer and similar control applications or
Special Features	Rejection Style

### Manufacturer Information

Brand	Eaton Bussmann series
GTIN	00051712497114
UPC	051712497114

### Taxonomies, Classifications, and Categories

Category Description	MIDGET FUSES
Type	FUSE

### Packaging

Carton	10
Weight Per each	0.02



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

204 Lake Road  
76426-0000, TX Bridgeport  
Phone: 940-683-5740  
Fax: 940-683-5299

---

## Uses, Certifications, and Standards

standard

RoHS Compliant, CE Marked

---