

# Eaton FNQ-R-3-1/2

Catalog Number: FNQ-R-3-1/2

Eaton Bussmann series FNQ-R fuse, 3.5 A, Class CC, Non-indicating, Ferrule end x ferrule end, 12 sec at 200%, 200 kAIC, Melamine tube, Standard, 600 V



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Bussmann series FNQ-R fuse	FNQ-R-3-1/2
<b>UPC</b>	<b>EAN</b>
051712496995	5027590060356
<b>Product Length/Depth</b>	<b>Product Height</b>
0.41 in	1.5 in
<b>Product Width</b>	<b>Product Weight</b>
0.41 in	0.15 lb
<b>Warranty</b>	<b>Compliances</b>
Not Applicable	RoHS Compliant CE Marked

## Product specifications

### Fuse indicator

Non-indicating

### Special features

Rejection style

### Interrupt rating

200 kAIC

### Type

Current-limiting high inrush time-delay fuse

### Connection

Ferrule end x ferrule end

### Response time

12 sec at 200%

### Class

Class CC

### Material

Melamine tube

### Voltage rating

600 V

### Application

Line protection, small control transformers, industrial control, branch circuits

### Amperage Rating

3.5 A

### Packaging type

Standard

## Resources

### Catalogs

Bussmann series complete full line catalog no. 1007

### Multimedia

Bussmann series Fuseology

### Specifications and datasheets

Eaton Specification Sheet - FNQ-R-3-1/2

### Technical data sheets

FNQ-R-3-1/2-FNQ-R-3-1-2-CLASS CC TIME DELAY