

Eaton FNQ-R-6

Catalog Number: FNQ-R-6

Eaton Bussmann series FNQ-R fuse, 6 A, Class CC, Non-indicating, Ferrule end x ferrule end, 12 sec at 200%, 200 kAIC, Melamine tube, Standard, 600 V



General specifications

Product Name	Catalog Number
Eaton Bussmann series FNQ-R fuse	FNQ-R-6
UPC	Product Length/Depth
051712497008	1.5 in
Product Height	Product Width
0.41 in	0.41 in
Product Weight	Warranty
0.15 lb	Not Applicable
Compliances	
CE Marked	
RoHS Compliant	

Electrical Ratings

Amperage Rating

6 A

Voltage rating

600 V

General Information

Application

Line protection, small control transformers, industrial control, branch circuits

Connection

Ferrule end x ferrule end

Special features

Rejection style

Physical Details

Type

Current-limiting high inrush time-delay fuse

Resources

Catalogs

[Bussmann series complete full line catalog no. 1007](#)

Multimedia

[Bussmann series Fuseology](#)

Specifications and datasheets

[Eaton Specification Sheet - FNQ-R-6](#)

Technical data sheets

[FNQ-R-6~CLASS CC TIME DELAY](#)

Technical service bulletins

[Datasheet - FNQ-30](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)