

Electrical Power Fuses

Type BAN 13/32" x 1-1/2" (10.3 mm X 38.1 mm) Fast Acting

Fiber; Formerly 5AB. Mounts in Buss fuseholders, fuseblocks, and clips. Rated at 250V.



Mfr.'s Type & Amp Rating	Each	Mfr.'s Type & Amp Rating	Each
BAN-1	2.98	BAN-10	2.84
BAN-2	2.98	BAN-12	2.98
BAN-3	2.98	BAN-15	2.84
BAN-4	2.98	BAN-20	2.84
BAN-5	2.98	BAN-25	2.98
BAN-6	2.98	BAN-30	2.68
BAN-8	2.98		

Type FNM 13/32" x 1-1/2" (10.3mm x 38.1mm) Time-Delay

Fiber. Formerly designed 5AG. A Dual element Fusetron fuse. For circuits with high inrush currents. Mount in Buss fuseholders, fuseblocks, and clips. U.L. File E19180; guide JDYX. CSA File 53787; Class 1422-01. Rated at 250 V to 10 A, 125V, 12-15 A and 32 V, 20-30A.



Mfr.'s Type & Amp Rating	Each	Mfr.'s Type & Amp Rating	Each
FNM-1/10	5.94	FNM-2-8/10	5.50
FNM-15/100	5.94	FNM-3	4.30
FNM-2/10	5.94	FNM-3-2/10	4.40
FNM-1/4	5.94	FNM-3-1/2	4.40
FNM-3/10	5.94	FNM-4	4.30
FNM-4/10	5.94	FNM-4-1/2	5.50
FNM-1/2	4.78	FNM-5	4.12
FNM-6/10	4.78	FNM-5-6/10	5.50
FNM-8/10	4.78	FNM-6	4.64
FNM-1	4.50	FNM-6-1/4	4.40
FNM-1-1/8	5.94	FNM-7	4.40
FNM-1-1/4	5.32	FNM-8	4.30
FNM-1-4/10	5.70	FNM-9	5.50
FNM-1-1/2	5.00	FNM-10	4.12
FNM-1-6/10	5.00	FNM-12	4.64
FNM-1- 8/10	5.50	FNM-15	4.12
FNM-2	4.12	FNM-20	4.30
FNM-2-1/4	5.30	FNM-25	4.90
FNM-2-1/2	4.64	FNM-30	4.30

Type FNW 13/32" x 1-1/2" (10.3mm x 38.1mm) Time-Delay

Melamine. Interrupting rating - 10,000AIC. Mount in Buss fuseholders, fuseblocks, and clips. U.L. File E19180; Guide JDYX. Rated at 250 V.



Mfr.'s Type & Amp Rating	Each	Mfr.'s Type & Amp Rating	Each
FNW-12	4.90	FNW-25	4.90
FNW-15	4.48	FNW-30	4.48
FNW-20	4.48		

Type KTK-R 13/32 x 1-1/2" (10.3mm x 38.1mm) Fast Acting, Class CC, Rejection Type

A Limitron fast acting fuse Melamine. U.L. Listed for branch circuit protection. Class CC. Rejection type; for both standard holders or those which reject other type fuses. Mount in Buss Class CC fuseblocks and Buss fuseholders HPS-RR (thru 30 amps). Interrupting rating - 200,000AIC. Current limiting. U.L. File 4273A; Guide JDDZ. CSA File 53787; Class 12422-01. Rated at 600 V.



Mfr.'s Type & Amp Rating	Each	Mfr.'s Type & Amp Rating	Each
KTK-R-1/10	14.06	KTK-R-4	11.24
KTK-R-1/8	14.06	KTK-R-5	10.54
KTK-R-2/10	14.06	KTK-R-6	11.06
KTK-R-1/4	14.06	KTK-R-7	12.90
KTK-R-3/10	14.06	KTK-R-8	11.24
KTK-R-4/10	14.06	KTK-R-9	14.16
KTK-R-1/2	11.16	KTK-R-10	10.54
KTK-R-3/4	12.14	KTK-R-12	10.72
KTK-R-1	10.54	KTK-R-15	10.54
KTK-R-1-1/12	10.54	KTK-R-20	10.54
KTK-R-2	10.54	KTK-R-25	11.24
KTK-R-3	10.54	KTK-R-30	10.54

Type FNQ 13/32" x 1-1/2" (10.3mm x 38.1mm) Time-Delay

Fiber. Interrupting rating - 10,000AIC. Mount in Buss fuseholders, fuseblocks, and clips. U.L. File E19180; Guide JDYX. CSA File 53787; Class 1422-01. Rated at 500 V.



Mfr.'s Type & Amp Rating	Each	Mfr.'s Type & Amp Rating	Each
FNQ-1/10	14.64	FNQ-3-2/10	12.38
FNQ-1/8	14.78	FNQ-3-1/2	13.36
FNQ-15/100	15.38	FNQ-4	11.82
FNQ-2/10	14.78	FNQ-4-1/2	14.36
FNQ-1/4	13.36	FNQ-5	11.82
FNQ-3/10	14.78	FNQ-5-6/10	14.36
FNQ-4/10	14.78	FNQ-6	11.82
FNQ-1/2	12.38	FNQ-6-1/4	15.22
FNQ-6/10	13.36	FNQ-7	12.38
FNQ-8/10	13.36	FNQ-8	11.82
FNQ-1	11.82	FNQ-9	15.22
FNQ-1-1/8	15.54	FNQ-10	11.82
FNQ-1-1/4	14.36	FNQ-12	11.82
FNQ-1-1/2	12.38	FNQ-14	15.84
FNQ-1-6/10	12.38	FNQ-15	11.82
FNQ-2	11.82	FNQ-20	11.82
FNQ-2-1/4	15.22	FNQ-25	11.82
FNQ-2-1/2	12.38	FNQ-30	11.82
FNQ-3	11.82		

Type SC 13/32" x 1-5/16" (to 2-1/4") Time-Delay (Except SC-1/2 to SC -6)

Highly compact branch circuit fuses; U.L. Class G. Applicable in 120/208, 120/240, and 277/480 volt circuits. Interrupting rating - 100,000AIC. Current limiting. Mount in type HPF fuseholders; also Buss Class G fuseblocks. Size varies with amp rating; prevent oversizing. For full information please call any of the toll free numbers on the back of this catalog and request Buss Catalog FLC. U.L. File E4273A; Guide JDDZ. Rated at 300 V.



Mfr.'s Type & Amp Rating	Each	Mfr.'s Type & Amp Rating	Each
SC-1/2	6.08	SC-15	3.76
SC-1	5.46	SC-20	3.96
SC-2	5.46	SC-25	9.04
SC-3	5.46	SC-30	7.04
SC-4	5.36	SC-35	8.36
SC-5	5.12	SC-40	7.80
SC-6	5.12	SC-45	8.86
SC-8	6.08	SC-50	8.86
SC-10	5.12	SC-60	7.66

Type KTK 13/32" x 1-1/2" (10.3mm x 38.1mm) Fast Acting

A Limitron fast acting fuse Melamine. Interrupting rating 100,000 AIC. Mount in Buss fuseholders, fuseblocks, and clips. U.L. File E 19180; Guide JDYX CSA File 53787; Class 1422-01. Rated at 600V.



Mfr.'s Type & Amp Rating	Each	Mfr.'s Type & Amp Rating	Each
KTK-1/10	12.28	KTK-4	10.06
KTK-1/8	12.82	KTK-5	9.86
KTK-2/10	12.82	KTK-6	8.58
KTK-1/4	10.82	KTK-7	11.62
KTK-3/10	12.82	KTK-8	10.06
KTK-1/2	10.62	KTK-9	12.82
KTK-3/4	11.62	KTK-10	9.86
KTK-1	9.86	KTK-12	11.58
KTK-1-1/2	10.72	KTK-15	9.86
KTK-2	9.86	KTK-20	9.90
KTK-2-1/2	12.28	KTK-25	9.90
KTK-3	9.86	KTK-30	9.90
KTK-3-1/2	12.82		

Type FNQ-R 13/32" x 1-1/2" (10.3mm x 38.1mm) Time-Delay, Class CC, Rejection Type

Construction: Melamine tube. Voltage Rating: 600 VAC. Interrupting Rating: 200,000A RMS Sym. Approvals: Std. 248-4, Class CC; UL Listed, Guide JDDZ, File E4273; CSA Certified, Class 1422-01, File 53787.



Mfr.'s Type & Amp Rating	Each	Mfr.'s Type & Amp Rating	Each
FNQ-R-1/4	14.10	FNQ-R-2-1/2	14.10
FNQ-R-4/10	15.60	FNQ-R-3	12.54
FNQ-R-1/2	12.54	FNQ-R-4	13.54
FNQ-R-6/10	15.60	FNQ-R-5	12.66
FNQ-R-8/10	13.88	FNQ-R-6	14.10
FNQ-R-1	12.38	FNQ-R-7-1/2	14.90
FNQ-R-1-1/2	12.66	FNQ-R-8	14.10
FNQ-R-2	12.66	FNQ-R-10	13.54



CBC is a full line BUSSMANN distributor. Consult us for complete information on products not shown in this catalog.