

Eaton FRN-R-3

Catalog Number: FRN-R-3

Eaton Bussmann series FRN-R fuse, 3 A, Dual, Class RK5, Non-indicating, Ferrule end x ferrule end, 8 sec at 500%, 200 kAIC at 250 V|20 kAIC at 125 Vdc, Standard, 250 V, 125 Vdc



General specifications

Product Name	Catalog Number
Eaton Bussmann series FRN-R fuse	FRN-R-3
UPC	Product Length/Depth
051712506991	0.56 in
Product Height	Product Width
0.56 in	0.56 in
Product Weight	Warranty
0.04 lb	Not Applicable
Compliances	
CE Marked	

Electrical rating

Amperage Rating

3 A

Interrupt rating

200 kAIC at 250 Vac

20 kAIC at 125 Vdc

Response time

8 sec at 500%

Voltage rating

250 Vac, 125 Vdc

Physical details

Number of elements

Dual

Packaging type

Standard

General information

Class

Class RK5

Connection

Ferrule end x ferrule end

Fuse indicator

Non-indicating

Special features

Finger safe, power loss 3.48 w

Resources

Catalogs

Bussmann series complete full line catalog no. 1007

Multimedia

Bussmann series Fuseology

Specifications and datasheets

Eaton Specification Sheet - FRN-R-3

Technical data sheets

FRN-R-3~FUSETRON DUAL-ELEMENT CLASS RK5

Technical service bulletins

Datasheet - FNQ-30



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)