

# Eaton FRN-R-35

Catalog Number: FRN-R-35

Eaton Bussmann series FRN-R fuse, 35 A, Dual, Class RK5, Non-indicating, Ferrule end x ferrule end, 10 sec at 500%, 200 kAIC at 250 V|20 kAIC at 125 Vdc, Standard, 250 V, 125 Vdc

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton Bussmann series FRN-R fuse	FRN-R-35
<b>UPC</b>	<b>Product Length/Depth</b>
051712101776	3 in
<b>Product Height</b>	<b>Product Width</b>
0.81 in	0.81 in
<b>Product Weight</b>	<b>Warranty</b>
1.95 lb	Not Applicable
<b>Compliances</b>	
CE Marked	

## Electrical rating

### Amperage Rating

35 A

### Interrupt rating

20 kAIC at 125 Vdc

200 kAIC at 250 Vac

### Response time

10 sec at 500%

### Voltage rating

250 Vac, 125 Vdc

## Physical details

### Number of elements

Dual

### Packaging type

Standard

## General information

### Class

Class RK5

### Connection

Ferrule end x ferrule end

### Fuse indicator

Non-indicating

### Special features

Finger safe

## Resources

### Catalogs

Bussmann series full line catalog 1007, section 01- low voltage branch circuit fuses

### Multimedia

Bussmann series Fuseology

### Specifications and datasheets

Eaton Specification Sheet - FRN-R-35

### Technical data sheets

FRN-R-35~FUSETRON DUAL-ELEMENT CLASS RK5

### Technical service bulletins

Datasheet - FNQ-30



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)