

# Eaton FRS-R-10

Catalog Number: FRS-R-10

Eaton Bussmann series FRS-R fuse, 10 A, Dual, Class RK5, Non-indicating, Ferrule end x ferrule end, 10 sec at 500%, 20 kAIC at 300 Vdc|200 kAIC at 600 V, Standard, 600 V, 300 Vdc

## General specifications

|                                  |                      |
|----------------------------------|----------------------|
| Product Name                     | Catalog Number       |
| Eaton Bussmann series FRS-R fuse | FRS-R-10             |
| UPC                              | Product Length/Depth |
| 051712508285                     | 7.88 in              |
| Product Height                   | Product Width        |
| 1.11 in                          | 1.11 in              |
| Product Weight                   | Warranty             |
| 0.4 lb                           | Not Applicable       |
| Compliances                      |                      |
| CE Marked                        |                      |



## Electrical rating

### Amperage Rating

10 A

### Interrupt rating

20 kAIC at 300 Vdc  
200 kAIC at 600 Vac

### Response time

10 sec at 500%

### Voltage rating

600 Vac, 300 Vdc

## Physical details

### Number of elements

Dual

### Packaging type

Standard

## General information

### Class

Class RK5

### Connection

Ferrule end x ferrule end

### Fuse indicator

Non-indicating

## Resources

### Multimedia

[Bussmann series Fuseology](#)

### Specifications and datasheets

[Eaton Specification Sheet - FRS-R-10](#)

### Technical data sheets

[FRS-R-10-FUSETRON DUAL ELEMENT FUSE CLASS RK5](#)

### Technical service bulletins

[Datasheet - FNQ-30](#)