



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FSD7810D 16AWG BLK SNGL Wire 10MM FML Pin TRML *Panduit Corporation*

| | |
|------------------|---|
| Catalog Number | FSD7810D |
| Manufacturer | Panduit Corporation |
| Description | Covered Ferrules Single Wire Black Din End Sleeve, 16 Awg, 10MM Pin Length. |
| Weight per unit | 0.1500 (lbs/each) |
| Product Category | Small Terminals & Connectors |

Features

| | |
|------------|---------------|
| insulation | Polypropylene |
| Material | Copper |
| media | Yes |
| Wire Size | 16 |

Material, Color, and Finish

| | |
|--------|--------|
| Color | Black |
| Finish | Tinned |

Descriptions

| | |
|------------------------|---|
| Description | 16AWG BLK SNGL WIRE 10MM FML PIN TRML |
| extra long description | PAN FSD78-10-D Pan-Term® FSD78-10-D |
| Long Description | Covered ferrules single wire black DIN end sleeve, 16 AWG, 10mm pin length. |
| Product Type | Pan-Term® FSD78-10-D Covered Single Wire Ferrules |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | PANDUIT |
| GTIN | 00074983762569 |
| Manufacturers Part Number | FSD78-10-D |
| UPC | 074983762569 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------|
| Category Description | Fuses & Fuse Accessories |
| Type | Covered Single Wire Ferrule |

Availability

| | |
|-------------|-----|
| minimum qty | 500 |
|-------------|-----|

Packaging

| | |
|-----------------|------|
| Carton | 500 |
| Weight Per each | 0.15 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------|--|
| Mounting | 17/32 |
| standard | DIN 46228, CSA C22.2 No. 291-14, UL 486F, cULus 486F |
| Temperature Rating | 221 Degrees Fahrenheit (105 Degrees Celsius) |