

Eaton FWH-600A

Catalog Number: FWH-600A

Eaton Bussmann series FWH high speed fuse, 1000 Vdc, 600A RMS, 200 kAIC at 1000 Vac, 50 kAIC at 500 Vdc, Non Indicating, High speed fuse, Blade end X blade end, Stud



General specifications

Product Name	Catalog Number
Eaton Bussmann series FWH high speed fuse	FWH-600A
	UPC
	051712150224
Product Length/Depth	Product Height
2.17 in	2.8 in
Product Width	Product Weight
5.3 in	0.92 lb
Warranty	Compliances
Not Applicable	CE Marked
	RoHS Compliant
Certifications	
UL Recognized	
CSA Certified	

Electrical rating

Amperage Rating

600A RMS

Interrupt rating

200 kAIC at 1000 Vac

50 kAIC at 500 Vdc

Voltage rating

1000 Vdc

Watt losses

108 W

Physical details

Packaging type

Standard

General information

Connection

Blade end x blade end

Fuse indicator

Non Indicating

Mounting method

Stud

Resources

Catalogs

[Bussmann series complete full line catalog no. 1007](#)

Specifications and datasheets

[Eaton Specification Sheet - FWH-600A](#)

Technical data sheets

[FWH-600A-BUSS HIGH SPEED FUSE](#)

[Bussmann series FWH 6x32mm high speed fuse data sheet no. 720038](#)

Technical service bulletins

[Datasheet - FNQ-30](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)