



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GASK015N 1/2" Form 5 Conduit Body Gasket

Crouse-Hinds

Catalog Number	GASK015N
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Condulet Series 5 Gasket, Neoprene, 1/2"
Weight per unit	0.0200 (lbs/each)
Product Category	Alum

Features

connection	Threaded / Set Screw
dimensions	1.3200 IN X 0.0600 IN X 3.8400 IN
Form	Series 5

Material, Color, and Finish

Color	Gray
Finish	Epoxy Powder Coat

Dimensions and Weight

Hub Size	1/2 in
----------	--------

Descriptions

extra long description	MIDWEST GASK015N 1/2 NEOPRENE GASKE
Features	Eaton's Crouse-Hinds Division Series 5 die cast copper-free aluminum conduit bodies, covers and gaskets are available for use with rigid or EMT conduit (with set screw). Conduit bodies are available in trade sizes 1/2" to 4", in the most popular conduit body shapes (C, LB, LL, LR, T) and 1/2" to 2" in TB and X shapes. The Series 5 family is available as components or pre-packaged in various configurations as a SnapPack assembly. In addition, Series 5 is completely interchangeable with other manufacturer
Long Description	Eaton Crouse-Hinds series Condulet Series 5 gasket, Neoprene, 1/2"
Product Type	1/2 Neoprene Gasket
Special Features	Corrosion Resistant

Manufacturer Information

Brand	Eaton
GTIN	00784564140715
Manufacturers Part Number	GASK015N
UPC	784564140715

Taxonomies, Classifications, and Categories

Category Description	FORM 5 CONDULETS, COVERS, & GASKETS
Type	Gasket



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	100
Weight Per each	0.02

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Enclosure	Condulet
Mounting standard	Conduit UL, cUL