

Specifications



Eaton GBB-2-R

Eaton AGC series Fast-acting fuse, 7A, 250 Vac, 32 Vdc (self certified), R

General specifications

PRODUCT NAME	Eaton Bussmann series very fast-acting fuse
CATALOG NUMBER	GBB-2-R
UPC	051712549912
EAN	5027590246682
PRODUCT HEIGHT	32 mm
PRODUCT DIAMETER	6 mm
PRODUCT WEIGHT	1.36 g
COMPLIANCES	CE Marked RoHS Compliant
GLOBAL CATALOG	GBB-2-R

Product specifications

AMPERAGE RATING	2 A
RESISTANCE	0.0662 ohms DC cold
VOLTAGE DROP	0.1687 mV typical
INTERRUPT RATING	200 AIC at 250 Vac 10 kAIC at 125 Vac/dc
FUSE INDICATOR	Non-indicating
CONNECTION	Ferrule end x ferrule end
RESPONSE TIME	2 min at 150%, 1 sec at 250%
MATERIAL	Ceramic tube Nickel-plated brass end cap construction
QUANTITY	5
VOLTAGE RATING	250 Vac, 125 Vdc
TYPE	Electronic
APPLICATION	Electronic circuits

Resources

PEP ECO-PASSPORT	EATO-00034-V01.01-EN
SPECIFICATIONS AND DATASHEETS	Eaton GBB ceramic tube fuses data sheet
	Eaton Specification Sheet - GBB-2-R

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
[Eaton.com](#)

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

