



BURNDY Catalog Number
UPC Number
Description
Status

GBM26
 7818102314499
 4SOL-2/0STR CU BAR 1 PC
 Active

Web Use
 BURNDY Product Line

Width (in)
 Height (in)
 Size (Hex) or Size (Bolt)
 Thickness
 Size (Hex) or Size (Bolt) - in
 Width (Fraction)

Dimensional
 1.50
 1.49
 3/8
 0.25
 0.38
 1-1/2

Product Description

General
 Mechanical Grounding Connector,
 Cable to 1/4" Thick Bar, 4 AWG
 (Sol)-2/0 AWG (Str), 3/8" Stud

Bar Thickness (Range)
 Copper Solid Size (Range)
 Copper Stranded (Range)

Conductor(s)
 N/A
 4 AWG-2/0 AWG
 4 AWG-2/0 AWG

Installation Torque
 Type of Plating
 Plated (Yes or No)
 Product Material

Physical
 240
 Unplated
 N
 Copper Alloy

Rated for Direct Burial
 UL Listed
 CSA Certified
 ROHS Compatible
 UL Recognized
 CULUS
 Industry Standards

Approvals / Certifications
 Y
 Y
 Y
 Exempt
 N
 N
 UL467

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175