



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## GC2525CT 6-1/0 1-Bolt Ground Conn *Burndy LLC*

Catalog Number	GC2525CT
Manufacturer	Burndy LLC
Description	Cast Copper Alloy Cable Tray Ground Clamp, #6 Sol. (.162 Dia.) -1/0 STR. (.372 Dia.), 1.12 In L, 1.45 In W, Tin Plated.
Weight per unit	0.2400 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Material	COPPER ALLOY
----------	--------------

### Descriptions

Description	6-1/0 1-BOLT GROUND CONN
extra long description	BUR GC2525CT 6SOL-1/0 STR CABLETRAY
Long Description	Cast Copper Alloy Cable Tray Ground Clamp, #6 Sol. (.162 Dia.) -1/0 Str. (.372 Dia.), 1.12 in L, 1.45 in W, Tin Plated.
Product Type	Mechanical
Special Features	Features: Made Of Tin-Plated Cast Copper Alloy, It Accommodates Either One Or Two Conductors, Copper Or Aluminum Cable, In Addition To A Low Profile Head With A Deep Phillips Recess, The Galvanized Steel Bolt Has A Ribbed Neck Which Prevents Rotation During Installation When Installed In A 0.44 Diameter Hole, When Used On Aluminum Conductor, The Cable Must Be Scratch Brushed And PENETROX A Joint Compound Must Be Used On Cable And Connector, UL467 Listed For Copper Conductor Only, Suitable For Direct Burial

### Manufacturer Information

Brand	BURNDY
GTIN	00781810035504
Manufacturers Part Number	GC2525CT
UPC	781810035504

### Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	GC-CT

### Packaging

Carton	1
Weight Per each	0.24



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

For Direct Burial Applications In Concrete Or Earth And For Used  
With Aluminum Or Galvanized Steel Cable Tray

standard

UL467