



BURNDY Catalog Number
UPC Number
Description
Status

GC3434
 7818102317533
 300-500 TWO CU CABLE
 Active

Web Use
 BURNDY Product Line

Width (in)
 Length (in)
 Height (in)
 Size (Hex) or Size (Bolt)
 Thickness
 Size (Hex) or Size (Bolt) - in
 Width (Fraction)

Dimensional
 2.56
 1.62
 2.82
 1/2
 0.25
 0.50
 2-5/9

Product Description

General

Mechanical Grounding Connector,
 2 Copper Cables to 1/4" Thick
 Bar, 300 kcmil - 500 kcmil, 1/2"
 Stud

Bar Thickness (Range)
 Copper Solid Size (Range)
 Copper Stranded (Range)

Conductor(s)

1/4 in
 N/A
 300 kcmil-500 kcmil

Installation Torque
 Type of Plating
 Plated (Yes or No)
 Product Material

Physical

480
 Unplated
 N
 Copper Alloy

Rated for Direct Burial
 UL Listed
 CSA Certified
 ROHS Compatible
 UL Recognized
 CULUS
 Industry Standards

Approvals / Certifications

Y
 Y
 Y
 Exempt
 N
 N
 UL467

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175