



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## GE232MAXGN 1-2 F32T8 Inst Start Ballast 120-277V Norm Bal Fac

*Ge By Current Lamps*

|                  |  |
|------------------|--|
| Catalog Number   | GE232MAXGN   |
| Manufacturer     | Ge By Current Lamps  |
| Description      | Ge Ultramax™, 60 HZ, Normal Ballast Factor, Instant Start, 9.5 In Length, 1.3 In Width, 1.18 In Height, 2 or 1-F32T8 |
| Weight per unit  | 1.2 (lbs/each)   |
| Product Category | Electronic Linear Fluorescent  |

### Features

|                |               |
|----------------|---------------|
| Ballast Factor | Normal        |
| start type     | Instant Start |

### Dimensions and Weight

|        |      |
|--------|------|
| Height | 1.18 |
| Length | 9.5  |
| Width  | 1.3  |

### Descriptions

|                        |  |
|------------------------|--|
| Description            | 1-2 F32T8 INST START BALLAST 120-277V NORM BAL FAC   |
| extra long description | GEL GE232MAX-G-N 72275 ELECTRONIC B  |
| Long Description       | GE UltraMax™, 60 Hz, Normal Ballast Factor, Instant Start, 9.5 IN Length, 1.3 IN Width, 1.18 IN Height, 2 or 1-F32T8 |
| Product Type           | 72275 Electronic Ballast   |
| Special Features       | GE232MAX-G-N (Replaces GE-232-MV-N) Designation  |

### Manufacturer Information

|                           |                      |
|---------------------------|----------------------|
| Brand                     | Ge Traditional Lamps |
| GTIN                      | 00043168722759       |
| Manufacturers Part Number | GE232MAX-G-N         |
| UPC                       | 043168722759         |

### Taxonomies, Classifications, and Categories

|                      |                                 |
|----------------------|---------------------------------|
| Category Description | ELECTRONIC BALLAST              |
| Type                 | Ballasts_Fluorescent_Electronic |

### Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Package         | 10   |
| Weight Per each | 1.17 |

### Uses, Certifications, and Standards

|                  |    |
|------------------|----|
| Frequency Rating | 60 |
|------------------|----|