

Eaton GFS1

Catalog Number: GFS1

Eaton Crouse-Hinds series GFS ground fault circuit interrupter, 20A, 5 mA, Copper-free aluminum, Factory sealed, 125 Vac



General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series GFS ground fault circuit interrupter	GFS1
	UPC
	782274278117
Product Length/Depth	Product Height
3.5 in	5.88 in
Product Width	Product Weight
2.63 in	2.15 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

NEMA Rating

3

7

9

12

Product specifications

Amperage Rating

20A

Ground trip current

5 mA

Voltage rating

125 Vac

Material

Copper-free aluminum

Special features

Factory sealed

Resources

Catalogs

[GFS Explosionproof Ground Fault Circuit Interrupter catalog page](#)

Certification reports

[GFS Explosionproof Ground Fault Circuit Interrupter Canadian certification](#)

[GFS Explosionproof Ground Fault Circuit Interrupter UL certification](#)

Installation instructions

[IF 1007 - GFS Ground Fault Circuit Interrupter](#)

[IF 1424 - DSD, GFS, CPS and ENR Replacement Covers](#)

Specifications and datasheets

[Eaton Specification Sheet - GFS1](#)