

Eaton GHB1015

Catalog Number: GHB1015

Eaton Series C complete molded case circuit breaker, G-frame, GHB, Complete breaker, Fixed thermal, Fixed magnetic trip type, Single-pole, 15 A, 277 Vac, 125 Vdc, 14 kAIC at 277 Vac, 50/60 Hz

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Series C complete molded case circuit breaker	GHB1015
	UPC
	786679023617

Product Length/Depth	Product Height
2.63 in	4 in

Product Width	Product Weight
1 in	0.7 lb

Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year Federal Specifications Classification W- from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	C375B
	Certifications
	UL Listed

defaultTaxonomyAttributeLabel

Type

Molded case circuit breaker

Amperage Rating

15 A

Voltage rating

277 Vac, 125 Vdc

Trip Type

Fixed thermal, fixed magnetic

Circuit breaker type

GHB

Circuit breaker frame type

Complete breaker

Series

Series C

Frame

G

Frequency rating

50/60 Hz

Interrupt rating

14 kAIC at 277 Vac

Number of poles

Single-pole

Resources

Application notes

[Application of Tap Rules to Molded Case Breaker Terminals](#)

[UL listed 100%-rated molded case circuit breakers](#)

[Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)

Brochures

[Plug-in adapters for molded case circuit breakers product aid](#)

[Circuit breaker motor operators product aid](#)

[Multi-wire lugs product aid](#)

[Current limiting Series C molded case circuit breakers product aid](#)

[MOEM MCCB Product Selection Guide](#)

[Motor protection circuit breakers product aid](#)

[Power metering and monitoring with Modbus RTU product aid](#)

[StrandAble terminals product aid](#)

[Breaker service centers](#)

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

[Molded case circuit breakers catalog](#)

Drawings

[G-frame Molded Case Circuit Breaker Drawing](#)

Installation instructions

[Series C GB/GHB/GDB Circuit Breakers - IL](#)

Multimedia

[Circuit Breakers Explained](#)

[Circuit breakers explained](#)

Specifications and datasheets

[Series C G-Frame Time Current Curves](#)

[Series C G-Frame molded case circuit breakers time current curves](#)

[Series C J-Frame molded case circuit breakers time current curves](#)

[Series C F-Frame molded case circuit breakers](#)

[MOEM MCCB product selection guide](#)

[Eaton Specification Sheet - GHB1015](#)

Time/current curves

[Type GHB/GHC/GD/GPS 2 and 3-pole, 15-100A Time Curve](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)