



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GHB1030 30A GHB 1P BKR *Eaton Corp*

Catalog Number	GHB1030
Manufacturer	Eaton Corp
Description	Eaton Series C Complete Molded Case Circuit Breaker, G-Frame, GHB, Complete Breaker, Fixed Thermal, Fixed Magnetic Trip Type, Single-Pole, 30 A, 277 Vac, 125 VDC, 14 Kaic At 277 Vac, 50/60 HZ
Weight per unit	0.6500 (lbs/each)
Product Category	1 Pole

Features

Current Rating	30 A
dimensions	2.6300 IN X 1.0000 IN X 4.0000 IN
frame	G
interrupt rating	14 kAIC at 277 Vac
media	Yes
Poles	1
Voltage Rating	277 Vac, 125 Vdc

Descriptions

Description	30A GHB 1P BKR
extra long description	ETN GHB1030 30A GHB 1P BKR
Features	Experience the superior quality of the Eaton Series C Molded Case Circuit Breaker. The Series C circuit breaker is ideal for panelboards, switchboards, motor control centers, and busway applications. Choose from a premier selection of trip units including thermal magnetic, electronic, and magnetic only switches. Available for systems up to 600 VAC or 250 VDC with current ratings up to 800A.
Long Description	Eaton Series C complete molded case circuit breaker, G-frame, GHB, Complete breaker, Fixed thermal, Fixed magnetic trip type, Single-pole, 30 A, 277 Vac, 125 Vdc, 14 kAIC at 277 Vac, 50/60 Hz
Product Type	30A GHB 1P BKR

Manufacturer Information

Brand	Eaton
GTIN	00786679016466
Manufacturers Part Number	GHB1030
UPC	786679016466



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	Molded case circuit breaker

Packaging

Carton	1
Weight Per each	0.65

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies and EOEMs - Other
standard	UL Listed,Federal Specifications Classification W-C375B