ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2250 West Broadway Road Suite 102
85202-0000, AZ Mesa
Phone: 623-900-2983
Fax: 623-900-2984



GHB2030 Type GHB BRKR 2P 30A 277/480VAC Max 125/250VDC Max

Eaton Corp

Catalog Number	GHB2030
Manufacturer	Eaton Corp
Description	Molded Case Circuit Breaker, 30 A, Non-Interchangeable Thermal Magnetic Tripping Mechanism, Bolt-On, 277/480 V Ac;125/250 V DC, G-Frame Frame, 50/60 HZ, 6.1 In Overall Height, 3.7 In Overall Length, 2.9 In Overall Width, 21 LB
Weight per unit	1.2 (lbs/each)
Product Category	2 Pole

Features

dimensions	2.6300 IN X 2.0000 IN X 4.0000 IN
frame	G
media	Yes
Poles	Two-pole

Descriptions

Description	TYPE GHB BRKR 2P 30A 277/480VAC MAX 125/250VDC MAX
extra long description	ETN GHB2030 GHB CB 2P 30A 277/480VA

Manufacturer Information

GTIN	00786679911211
UPC	786679911211

Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	Molded case circuit breaker

Packaging

Carton	1
Package	12
Weight Per each	1.15

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & EOEM - Electrical Assemblies and EOEMs - Other
standard	UL Listed,Federal Specifications Classification W-C375B