

# Eaton GLL 4

Catalog Number: GLL 4

Eaton Crouse-Hinds series GLL grounding bushing, Rigid/IMC, Aluminum lug, #4-14 AWG, Malleable iron, 105°C temperature rating, Threaded, 1-1/4"



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Crouse-Hinds series GLL grounding bushing	GLL 4
	UPC
	784564123046
<b>Product Length/Depth</b>	<b>Product Height</b>
2 in	0.81 in
<b>Product Width</b>	<b>Product Weight</b>
2 in	0.19 lb

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

## Product specifications

### Conduit type

Rigid/IMC

### Temperature rating

105°C

### Lug material

Aluminum

### Thread

Threaded

### Trade size

1-1/4"

### Lug size

#4-14 AWG

### Material

Malleable iron

## Resources

### Catalogs

[Crouse-Hinds series Grounding Bushings - Rigid-IMC catalog page](#)

### Certification reports

[Grounding Bushings - Rigid-IMC UL certification](#)

[Grounding Bushings - Rigid-IMC Canadian certification](#)

### Specifications and datasheets

[Eaton Specification Sheet - GLL 4](#)