



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## GLL8 3" Mall Ins Ground Bushing

*Crouse-Hinds*

|                  |   |
|------------------|---|
| Catalog Number   | GLL8  |
| Manufacturer     | Crouse-Hinds  |
| Description      | Grounding Bushing, 3 In Trade Size, GLL Model, Insulated, #8 to 1/0 Awg Cable Size, 1 In Height, 4 In Diameter, 70 LB/100 |
| Weight per unit  | 0.7200 (lbs/each)   |
| Product Category | Rigid Conduit Fittings - Steel  |

### Features

|            |   |
|------------|---|
| connection | Threaded                                  |
| dimensions | 4.0000 IN X 4.0000 IN X 1.0000 IN         |
| Material   | Malleable Iron Body, Plastic Throat Liner |

### Dimensions and Weight

|      |      |
|------|------|
| Size | 3 in |
|------|------|

### Descriptions

|                        |  |
|------------------------|--|
| Description            | 3" MALL INS GROUND BUSHING   |
| extra long description | MIDWEST GLL 8 3 GRND BUSH 105C INSU  |
| Features               | Crouse-Hinds series grounding bushings are used with threaded and threadless rigid/IMC conduit to provide a means of grounding conduit through an insulated bushing. |

### Manufacturer Information

|       |                |
|-------|----------------|
| Brand | Eaton          |
| GTIN  | 00784564123084 |
| UPC   | 784564123084   |

### Taxonomies, Classifications, and Categories

|                      |   |
|----------------------|---|
| Category Description | Locknuts, Bushings, Re-Bushings, Re-Washers, Threaded Plugs, Knockout Plugs |
| Type                 | Grounding bushing   |

### Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Package         | 5    |
| Weight Per each | 0.72 |

### Uses, Certifications, and Standards

|                    |   |
|--------------------|---|
| Application        | Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other |
| standard           | UL, CSA   |
| Temperature Rating | 105 DEG C   |