



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2900 East Pioneer Parkway Suite 170
76010-0000, TX Arlington
Phone: 817-695-1616
Fax: 817-633-9062



GMA3R 3A 250V Fa 5X20MM Glass Fuse

Bussmann Fuses

Catalog Number	GMA3R
Manufacturer	Bussmann Fuses
Description	Fuse, Fast Acting Fuse Speed, 60 Min @ 135%;2 Min @ 200 % Response Time, Ferrule End X Ferrule End Connection, 3 A, 250 V Ac, Glass (Body);Brass(End Cap) Material, Ferrule Terminal, 5.2 MM Diameter, 20 MM Overall Length
Weight per unit	0.0050 (lbs/each)
Product Category	Small Dimension Fuses

Features

amperage rating	3 A
connection	Ferrule End X Ferrule End
dimensions	X X 0.7874 IN

Dimensions and Weight

Size	5 mm Diameter X 20 mm Length
------	------------------------------

Descriptions

Description	3A 250V FA 5X20MM GLASS FUSE
extra long description	EFSE GMA-3-R GMA 3A BUSS FUSE
Features	Fast-acting, glass tube 5 mm x 20 mm ferrule fuse designed to UL 248-14 for overcurrent protection of electronic circuits. Install into a Bussmann Series fuse holder, block or fuse clip. Also available with axial leads for thru-hole installation Eaton's GMA fast-acting, glass tube 5mm x 20mm ferrule fuses are designed to UL 248-14 for overcurrent protection of electronic circuits. Order in cartridge fuse format and install into a Bussmann Series fuse holder, block, or fuse clip, or purchase with available
Special Features	Low Breaking Capacity, Interrupt Rating 100 Amp at 250 Vac, 10 kA at 125 Vac, Material Glass Tube, Nickel Plated Brass Endcap, ROHS Complaint

Manufacturer Information

Brand	Eaton
GTIN	00051712647946
UPC	051712647946

Taxonomies, Classifications, and Categories

Category Description	GLASS FUSES (and ceramic)
Type	Fast-Acting Fuse

Packaging

Carton	5
Weight Per each	0.005



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2900 East Pioneer Parkway Suite 170
76010-0000, TX Arlington
Phone: 817-695-1616
Fax: 817-633-9062

Uses, Certifications, and Standards

standard

RoHS Compliant,CE Marked
