



Fast-Acting Fuse

BK/GMA-5-R

UPC:051712647342

Dimensions:

Height: .788 INLength: .197 INWidth: .197 IN

Weight: .002 LB

Warranties:

Not Applicable

Specifications:

Type: Electronic- small dimensionApplication: Electronic circuits

• Amperage Rating: 5A

• Voltage Rating: 125 Vac, 32 Vdc (self certified)

• Interrupt Rating: 10 kAIC at 125 Vac

Fuse Indicator: Non IndicatingPackaging Type: Standard

• Used With: out axial leads

• Response Time: 60 min maximum at 135%, 2

min maximum at 200%

Material: Glass tube, nickel-plated brass

endcaps

• Connection: Ferrule end X ferrule end

• Quantity: Bulk 100

Supporting documents:

• GMA 5A BUSS FA BK 100 BOX -R

Certifications: No Data

Product compliance:

CE Marked

RoHS Compliant



© 2016 Eaton. All rights reserved.