



Powering Business Worldwide

pe.eaton.com



Medium Time-Delay Fuse

GMC-1-R

UPC:051712642811

Dimensions:

- **Height:** .25 IN
- **Length:** .75 IN
- **Width:** .25 IN

Weight:.002 LB

Warranties:

- Not Applicable

Specifications:

- **Type:** Electronic- small dimension
- **Application:** Electronic circuits
- **Amperage Rating:** 1A
- **Voltage Rating:** 250 Vac, 32 Vdc (self certified)
- **Interrupt Rating:** 35 AIC at 250 Vac, 10 kAIC at 125 Vac
- **Fuse Indicator:** Non Indicating
- **Packaging Type:** Standard
- **Used With:** out axial leads
- **Response Time:** 60 min maximum at 135%, 2 min maximum at 200%
- **Material:** Glass tube, nickel-plated brass endcaps
- **Connection:** Ferrule end X ferrule end

Supporting documents:

- [GMC 1A BUSS FUSE](#)

Certifications: No Data

Product compliance:

- CE Marked
 - RoHS Compliant
-



Powering Business Worldwide

pe.eaton.com



Medium Time-Delay Fuse

GMC-1-R

UPC:051712642811

Dimensions:

- **Height:** .25 IN
- **Length:** .75 IN
- **Width:** .25 IN

Weight:.002 LB

Warranties:

- Not Applicable

Specifications:

- **Type:** Electronic- small dimension
- **Application:** Electronic circuits
- **Amperage Rating:** 1A
- **Voltage Rating:** 250 Vac, 32 Vdc (self certified)
- **Interrupt Rating:** 35 AIC at 250 Vac, 10 kAIC at 125 Vac
- **Fuse Indicator:** Non Indicating
- **Packaging Type:** Standard
- **Used With:** out axial leads
- **Response Time:** 60 min maximum at 135%, 2 min maximum at 200%
- **Material:** Glass tube, nickel-plated brass endcaps
- **Connection:** Ferrule end X ferrule end

Supporting documents:

- [GMC 1A BUSS FUSE](#)

Certifications: No Data

Product compliance:

- CE Marked
 - RoHS Compliant
-

