



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GMC5A 5A 125V Med TD Glass Fuse

Bussmann Fuses

Catalog Number	GMC5A
Manufacturer	Bussmann Fuses
Description	5A 125V 5MM X 20MM Glass, Medium Time Delay Fuse
Weight per unit	0.0040 (lbs/each)
Product Category	Tools & Testers

Features

amperage rating	5 Amp
connection	Ferrule End X Ferrule End
Response Time	60 Min Maximum at 135%, 2 Min Maximum at 200%
type of indicators	Non-Indicating
Voltage Rating	125 VAC

Dimensions and Weight

Size	5 mm Diameter X 20 mm Length
------	------------------------------

Descriptions

Description	5A 125V MED TD GLASS FUSE
extra long description	EFSE GMC-5A UL Medium Time Delay 5m
Long Description	5A 125V 5mm x 20mm Glass, Medium Time Delay Fuse
Product Type	UI Medium Time Delay 5MM Glass Fuse 5a
Special Features	Interrupt Rating 10000 Amp at 125 Vac, Material Glass Tube, Nickel Plated Brass Endcap, Low Breaking Capacity

Manufacturer Information

Brand	Cooper Bussmann North America
GTIN	00051712143288
Manufacturers Part Number	GMC-5A
UPC	051712143288

Taxonomies, Classifications, and Categories

Category Description	GLASS FUSES (and ceramic)
Type	Electronic, Medium Time Delay

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
Package	5
Weight Per each	0.004



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Electronic Circuits
standard	UL 248-14, CSA