



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GR8232AUNVEB81U 2 Lamp, 1'X4' Static Lensed Troffer, Electronic Ba *Cooper Lighting Solutions*

Catalog Number	GR8232AUNVEB81U
Manufacturer	Cooper Lighting Solutions
Description	2 Lamp, 1'X4' Static Lensed Troffer, Cee Listed Electronic Ballast, T8
Weight per unit	16.2 (lbs/each)
Product Category	Lighting

Features

amperage rating	0.116 at (277V)
Ballast Type	Instant Start
Lamp Type	T8 (Not Included)
Material	Steel
Number of Lamps	2
Voltage Rating	120-277V

Material, Color, and Finish

Style	(blank)
-------	---------

Descriptions

Description	2 LAMP, 1'X4' STATIC LENSED TROFFER, ELECTRONIC BA
extra long description	CLS GR8-232A-UNV-EB81-U GR8 2 LMP,
Long Description	2 Lamp, 1'x4' Static Lensed Troffer, CEE Listed Electronic Ballast, T8
Product Type	GR8 2 LMP, 1'X4' FL Trof, Elt Bal, T8
Special Features	Optimized for T8 lamps

Manufacturer Information

Brand	METALUX
GTIN	00662401551330
Manufacturers Part Number	GR8-232A-UNV-EB81-U
UPC	662401551330

Taxonomies, Classifications, and Categories

Category Description	Fluorescent Fixtures & Accessories
Type	Recessed Static

Packaging

Carton	1
Weight Per each	16.2

Uses, Certifications, and Standards

Application	lighting
Mounting	Troffer
standard	UL/cUL Listed - Damp Location