



SKU: GSW-16

UPC: 0032076890162

Features & Benefits:

Description: DPDT Toggle Switch

Specs

Dimensions

Lead Length	None
-------------	------

Additional Class Attributes

Control Style	2-Pole
Illuminated	No
Mounting Method	Recessed
Number of Positions	3
Speeds	2
Switch Outlet Grade	Commercial
Switch Style	Standard
Switch Type	Toggle
Warranty	1 Year
Wattage	2500

Material and Finish

Material	Nickel
----------	--------

Additional Technical Specifications

Connector Amperage Rating CU (Derated where applicable)	10 Amps
Contact Arrangement	DPDT
Contact Type	Maintained
Terminal Type	Screw

Testing Standards

Prop65 Compliance

WARNING: Cancer and Reproductive Harm -
www.P65warnings.ca.gov

Color

Color	Chrome
-------	--------

Voltage

Maximum Voltage	250 V
Minimum Voltage	125 V

Environment and Temperature

Environmental Conditions	Indoor
--------------------------	--------

General

Bag Quantity	1
Carton Quantity Description	STD PACK QTY 5
UPC Code	03207689016