



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GT2MV 2 Lamp, 2'X4' Static Lensed Troffer, Elec Ballast *Lithonia Lighting*

Catalog Number	GT2MV
Manufacturer	Lithonia Lighting
Description	Lith GT2 MV Recessed General Purpos
Weight per unit	19.6 (lbs/each)
Product Category	Fluorescent Recessed Architect

Features

Ballast Type	Electronic Ballast
Hardware	Yes
Lamp Included	NO
Lamp Type	Fluorescent
Material	Steel
Maximum Operating Temperature	25
Number of Lamps	2
pallet quantity	28
Shape	Rectangular
Voltage Rating	120-277
Warranty	2
Wattage	64

Material, Color, and Finish

Color	White
Finish	Gloss
Lens Color	Clear
Lens Material	Acrylic
Style	Traditional

Dimensions and Weight

Height	3.5
Length	48.5
Width	24.0000

Descriptions

Description	2 LAMP, 2'X4' STATIC LENSED TROFFER,ELEC BALLAST
Long Description	LITH GT2 MV Recessed General Purpos
Product Type	Troffer

Manufacturer Information

Brand	Lithonia Lighting
GTIN	00745975081714
Manufacturers Part Number	GT2 MV
UPC	745975081714



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Fluorescent Fixtures & Accessories
Type	Troffer

Trade Size

aperture size	2x4
---------------	-----

Availability

Manufacturer Status	Inactive
---------------------	----------

Packaging

Carton	1
Weight	19
Weight Per each	19.6

Uses, Certifications, and Standards

Application	Education, Offices & Banks, Retail
environmental conditions	Indoor
Mounting	Recessed
standard	UL