



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## GT4LWMV 2X4 Lensed TROFFER4, (4) *Lithonia Lighting*

Catalog Number	GT4LWMV
Manufacturer	Lithonia Lighting
Description	Lensed Troffer, T4 Bulb Shape, 48 In Length, 24 In Width, 3-1/8 In/7.9 CM Height, 120 to 277 V, 32 W, Electronic Ballast, Instant, White, 2850 LM Brightness (Lumens), Bi-Pin Base, 4100 K, 4 Lamps, 1 Ballasts, Steel Housing Material, Baked White Enamel, Recessed Mount, 23.7 LB/Ea
Weight per unit	23.7 (lbs/each)
Product Category	Fluorescent Recessed Architect

### Features

Hardware	Yes
Lamp Included	Yes
Lamp Type	Fluorescent
Material	Steel
Maximum Operating Temperature	25
pallet quantity	28
Power Source	Hardwired
Shape	Rectangular
Socket Type	Bi-pin: Single
Warranty	2
Wattage	128

### Material, Color, and Finish

Lens Color	Clear
Style	Traditional

### Descriptions

Description	2X4 LENSED TROFFER4, (4)
-------------	--------------------------

### Manufacturer Information

GTIN	00745975081707
UPC	745975081707

### Taxonomies, Classifications, and Categories

Category Description	Fluorescent Fixtures & Accessories
Type	Troffer

### Trade Size

aperture size	2x4
---------------	-----

### Availability

Manufacturer Status	Inactive
---------------------	----------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	23.7

## Uses, Certifications, and Standards

environmental conditions	Indoor
Mounting	Recessed
standard	UL