

## Specification Sheet

Part Number: GT.75X9000



Features quick release for repetitive access to cable and wire.

Can be opened and closed numerous times without failure.

Adjustable so one size can accommodate multiple bundle sizes.

Grip Tie Roll, 900" Long, 0.75" Wide, PA6/PP, Black, 1/pkg

Article Number 854-44396

Type GT.75X900

Color Black (BK)

Quantity Per pack

Product Description HellermannTyton Grip Ties are low-profile, one-piece fastening devices. Constructed of a hook and loop design, laminated back to back, the Grip Tie features quick release for repetitive access to cable and wire. Custom-cut lengths are available in various colors in a 5 yard roll and standard black up to a 25 yard roll. Ideal for job site applications, desired lengths can be cut on the spot.

Short Description Grip Tie Roll, 900" Long, 0.75" Wide, PA6/PP, Black, 1/pkg

Global Part Name GT.75X900

Length L (Imperial) 75.0

Length L (Metric) 22.9

Width W (Imperial) 0.75

Width W (Metric) 19.05

Material Polyethylene (PE) Polyamide (PA)

Material Shortcut PE PA

UV Resistant (Yes/No) No

Use Conditions For Indoor Use Only

Reach Compliant (Article 33) No

Package Quantity (Imperial) 1

Package Quantity (Metric) 1

Customs Number 3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)