

# Eaton GUAM16

Catalog Number: GUAM16

Eaton Crouse-Hinds series Condulet GUA conduit outlet box with cover, 3" cover opening diameter, Feraloy iron alloy, M shape, 1/2"

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton Crouse-Hinds series Condulet GUA conduit outlet box with cover	GUAM16
	<b>UPC</b>
	782274465708
<b>Product Length/Depth</b>	<b>Product Height</b>
4.38 in	4.38 in
<b>Product Width</b>	<b>Product Weight</b>
2.88 in	2.45 lb

## Certifications and compliances

### Area classification

Hazardous/Classified Locations

### Standards type

NEC/CEC

### NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

### NEMA Rating

3

4

7

9

## Product specifications

### Shape

M

### Trade size

1/2"

### Cover opening diameter

3"

### Material

Feraloy iron alloy

## Resources

### Catalogs

[Crouse-Hinds series GUA Conduit Outlet Boxes catalog page](#)

### Certification reports

[Condulet GUA and GUR Explosionproof Conduit Outlet Boxes UL certification](#)

### Installation instructions

[IF 1730 - GUA/EAB/EAJ Condulet Outlet Boxes](#)

### Specifications and datasheets

[Eaton Specification Sheet - GUAM16](#)

### Technical service bulletins

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)