

Eaton GUSC2013 AH

Catalog Number: GUSC2013 AH

Eaton Crouse-Hinds series GUSC snap switch, 20A/30A, Three-pole, With switch, 2 x 3/4" NPT entries, 2 HP, Feraloy iron alloy, Through feed, 3/4", 250/600 Vac

General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series GUSC snap switch	GUSC2013 AH
	UPC
	782274477503
Product Length/Depth	Product Height
6.06 in	6.19 in
Product Width	Product Weight
4.13 in	7.85 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

NEMA Rating

3

7

9

12

Product specifications

Enclosure type

With switch

Configuration

Three-pole

Voltage rating

250/600 Vac

Amperage Rating

20A/30A

Horsepower

2 hp

Trade size

3/4"

Style

Through feed

Entry size

2 x 3/4" NPT

Material

Feraloy iron alloy

Resources

Catalogs

[GUSC Series Explosionproof Snap Switches catalog page](#)

Certification reports

[GUSC Explosionproof Snap Switches UL certification](#)

Installation instructions

[IF 1712 - GUSC Snap Switches](#)

Specifications and datasheets

[Eaton Specification Sheet - GUSC2013 AH](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)