



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## GUV1384 U Bolt Ground Clamp

*Abb Installation Products, Inc*

Catalog Number	GUV1384
Manufacturer	Abb Installation Products, Inc
Description	U-Bolt Copper Ground Clamp, Stainless Steel U-Bolt, Wire Range 8 - 4 Awg, Rod Size 1-3/8 - 1-1/2 Inches, Ips Pipe Size Max 1-1/4 Inches, Length 3-7/16 Inches, Width 2-15/16 Inches, Depth 1-9/16 Inches
Weight per unit	0.8740 (lbs/each)
Product Category	Ground Rods & Grounding System

### Features

Conductor Size	8 - 4 AWG
insulation	No

### Material, Color, and Finish

Conductor Material	Copper
--------------------	--------

### Dimensions and Weight

Length	3-7/16 in
--------	-----------

### Descriptions

Description	U BOLT GROUND CLAMP
extra long description	ABB GUV1384 U BOLT GRD CLAMP COND 4
Long Description	U-Bolt Copper Ground Clamp, Stainless Steel U-Bolt, Wire Range 8 - 4 AWG, Rod Size 1-3/8 - 1-1/2 Inches, IPS Pipe Size Max 1-1/4 Inches, Length 3-7/16 Inches, Width 2-15/16 Inches, Depth 1-9/16 Inches
Product Type	U Bolt GRD Clamp Cond 4-8
Special Features	Excellent for connecting copper or copper-clad steel grounding conductor to ground rod or pipe. Specially designed spacer provides proper alignment between cable and electrode and affords more positive contact area

### Manufacturer Information

Brand	Blackburn Grounding
GTIN	00783786803583
Manufacturers Part Number	GUV1384
UPC	783786803583

### Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	GROUND CLAMP



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton ..... 10

Weight Per each ..... 0.874

## Uses, Certifications, and Standards

standard ..... UL E3060, CSA 12798