



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



H750RICAT 6" Ic At Led Remodel Can

Cooper Lighting Solutions

Catalog Number	H750RICAT
Manufacturer	Cooper Lighting Solutions
Description	6" Led Housing, Ic Air-Tite, Remodel, For Listed Halo Led Modules
Weight per unit	1.5 (lbs/each)
Product Category	Lighting

Features

amperage rating	0.167 at (120V)
Ballast Type	N/A
Lamp Type	LED (Not Included)
Number of Lamps	N/A
Socket Type	Quick Connect (No Socket)
Voltage Rating	120/277V
Wattage	N/A

Descriptions

Description	6" IC AT LED REMODEL CAN
extra long description	CLS H750RICAT 6"AIR-TITE IC LED REM
Long Description	6" LED Housing, IC Air-Tite, Remodel, for listed Halo LED Modules
Product Type	6"Air-Tite Ic Led Remodel Hous (New CTN)
Special Features	Use with HALO 6" RL56, RA56 and ML56 600, 900, 1200 series modules

Manufacturer Information

Brand	HALO
GTIN	00623961052248
Manufacturers Part Number	H750RICAT
UPC	623961052248

Taxonomies, Classifications, and Categories

Category Description	All Recessed Cans & Trims
Type	6" LED Housing

Packaging

Carton	1
Weight Per each	1.5499

Uses, Certifications, and Standards

Application	lighting
standard	UL/cUL Listed - Wet Location;Airtite;RoHS Compliant