

Twist-Lock® Devices
 20A, 250V AC, 2 Pole, 3 Wire Grounding
 Insulgrip® Plug

HUBBELL

Features

- Ribbed nylon housing provides a secure grip and impact and chemical resistance.
- Superior cord grip design protects terminations from excess strain.
- Clear, funnel shaped wire entry for ease of termination.
- Integral dust shield protects wiring chamber from dust or contaminants.



Ordering Information

| Description | Cord Diameter | UPC | Catalog Number |
|------------------------|--------------------|--------------|----------------|
| Black and white nylon. | .360"-.930" (9-24) | 783585037820 | HBL2321 |

Listings

Listed to UL 498
 Fed.Spec. W-C-596
 Certified to CSA C22.2 No.42

Specifications

| | |
|----------------------|---|
| Housing / Cord Clamp | Nylon |
| Terminal Retainer | Clear polycarbonate |
| Blades | Brass |
| Terminal Screws | #10-32 Brass (Phillips / Slotted / Robertson) |
| Terminal Clamp | Cold rolled steel – nickel plated |
| Assembly Screws | Steel - nickel plated |

Performance

Electrical

| | |
|----------------------|--|
| Current Interrupting | Certified for current interrupting at full rated current |
| Dielectric Voltage | Withstands 2,000V minimum |


Mechanical

| | |
|------------------------|---|
| Terminal Accommodation | #16 AWG - #8 AWG stranded copper wire only. |
|------------------------|---|

| | |
|-------------------------|--|
| Terminal Identification | Terminals identified in accordance with UL 498 |
|-------------------------|--|

Environmental

| | |
|------------------------|--|
| Flammability | HB or better per UL94 or CSA 22.2 No. 0.6 |
| Moisture Resistance | IP20 Suitability |
| Operating Temperatures | Maximum Continuous 75°C Minimum -40°C (w/o impact) |



Accessories

| | |
|--------------------|---------|
| Connector | HBL2323 |
| Single Receptacle | HBL2320 |
| Flanged Receptacle | HBL2326 |
| Weatherproof Boot | HBL6031 |

Resources

Customer Use Drawing
 eCatalog

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

