



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **HBL2341 LKG Plug, 20A 480V, L8-20P, B/W** *Hubbell Wiring Devices*

Catalog Number	HBL2341
Manufacturer	Hubbell Wiring Devices
Description	Locking Devices, Twist-Lock®, Industrial, Male Insulgrip® Plug, 20A 480V Ac, 2-Pole 3-Wire Grounding, Nema L8-20P, Screw Terminal, Black and White Nylon.
Weight per unit	0.3000 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

### **Features**

amperage rating	20
connection	Screwed Terminal
Cord Type	All Listed Portables
Current Rating	20
Material	Nylon
Number of Wires	3-Wire
pallet quantity	3060
Phase	1
Poles	2-Pole
Voltage Rating	480
Wattage	9
Wire Size	#16 to #8

### **Dimensions and Weight**

Size	2.26 in x 2.26 in x 2.75 in
------	-----------------------------

### **Descriptions**

Description	LKG PLUG, 20A 480V, L8-20P, B/W
extra long description	HWDK HBL2341 LKG PLUG, 20A 480V, L8
Long Description	Locking Devices, Twist-Lock®, Industrial, Male Insulgrip® Plug, 20A 480V AC, 2-Pole 3-Wire Grounding, NEMA L8-20P, Screw Terminal, Black and White Nylon.
Product Type	LKG Plug, 20A 480V, L8-20P, B/W
Special Features	Standard Product

### **Manufacturer Information**

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585037950
Manufacturers Part Number	HBL2341
UPC	783585037950



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES
Type	Plugs

## Packaging

Carton	1
Package	30
Weight Per each	0.3

## Uses, Certifications, and Standards

Application	Extra Heavy Duty Industrial
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Cord
nema rating	L8-20P
standard	Certified to CSA C22.2 No.42;Fed.Spec. W-C-596;Listed to UL 498