



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HBL2620ST LKG RCPT, 30A 250V, L6-30R, BK, Spring T *Hubbell Wiring Devices*

Catalog Number	HBL2620ST
Manufacturer	Hubbell Wiring Devices
Description	30A, 250V Edgeconnect™ Twist-Lock® Receptacle With Spring Termination
Weight per unit	0.3000 (lbs/each)
Product Category	Wiring Devices

Features

connection	Spring Termination
Dielectric Strength	Withstands 2,000V minimum
insulation	N/A
Material	Nylon
Number of Wires	3
pallet quantity	3060
Phase	1
Poles	2
Voltage Rating	250 V
Wattage	7,500
Wire Size	14 - 10 solid, 14 - 8 stranded (including compact stranded)

Dimensions and Weight

Size	3.28 in x 1.70 in x 1.47 in;Standard Sized Product
------	--

Descriptions

Description	LKG RCPT, 30A 250V, L6-30R, BK, SPRING T
extra long description	HWDK HBL2620ST LKG RCPT, 30A 250V,
Long Description	30A, 250V EdgeConnect™ Twist-Lock® Receptacle with Spring Termination
Product Type	LKG RCPT, 30A 250V, L6-30R, BK, Spring T
Special Features	Twist-Lock Receptacle with Spring Termination

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585569574
Manufacturers Part Number	HBL2620ST
UPC	783585569574

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
----------------------	----------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	50
Weight Per each	0.3

Uses, Certifications, and Standards

Application	Heavy Duty Industrial
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	I6-30R
standard	CSA Certified to Specification C22.2 No. 42;UL Listed To UL 498